

Racks

Server Frame 4-Post

48" Depth, M6 Cage Nut



Features

- Steel construction provides strength for heavy server and network equipment loading
- Ladder tray mounting provisions designed into top cross members
- Each rack unit numbered

Ordering Information

Rack Units	Finish	Catalog Number	UPC
45	Black powder coat	SF841948	662620249100

Listings

UL 1863
EIA/ECA-310-E Universal Mounting Pattern

Specifications

Height	84" (2134)
Depth	48" (1219)
Width	20" (514)
Hole Type	M6 Cage Nut
Material	Steel
Gauge	12 ga

Characteristics


Load Capacity	2,000 lb
Equipment	Supports 19" EIA wide rack-mount equipment
Thread Holes	M6 Cage Nut
Rack Units	Numbered

Accessories

Isolation Pad	HRRP
M6 Cage Nut pack	CKM6
1U Horizontal cable manager	HS13C
2U Horizontal cable manager	HS23C
6" Wide vertical cable manager	VS76H

Online Resources

Customer Drawing
Customer Use Drawing
eCatalog



Dimensions- inches (mm)

A	84" (2134)
B	3" (76)
C	48" (1219)
D	20.2" (513)

