

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 2-Circuit, 4) Duplex

By Hubbell Premise Wiring
Catalog # [PT206218](#)

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 6', 20A 125V, 2-Circuit, 4) Duplex

Features

- Available in 5 ft. or 6 ft. lengths
- Multiple spacing configurations
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes

Performance

Electrical - Crush Resistance - 300 lbs., Electrical - Impact Resistance - 5 ft. lbs, Electrical - Receptacle Rating - NEMA 5-15R & 5-20R, Environmental - Flame Rating - UL94V-0, Environmental - Temperature Range - -25.6° to 158° F, Mechanical - Wire - #12 AWG Stranded Copper

Specifications

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	Contact Manufacturer

Conductor

Wire Size	#12 AWG THHN
-----------	--------------

Configuration

Number Of Receptacles	4
-----------------------	---

Current

Current / Amperage Rating	20 A
Voltage Rating	125 VAC



Dimensions

Length	6 ft
--------	------

General

Item Type	Pre-Wired PlugTrak
Type	Two Circuits
Series	Non-Metallic
Specifications	• Material - UV Stabilized PVC • Number of Receptacles - 4 Duplex • PlugTrak Amperage - 20A • PlugTrak Length - 6 Foot • Receptacle Face - Thermoplastic • Spacing - 18 Inch
UPC	783585091105
Style	Standard
Color	Office White

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)