

HUBBELL
Premise Wiring

Complete Unit With 20A IG Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Gray

By Hubbell Premise Wiring
Catalog # [PT7IGFSDGYA](#)

Complete Unit With 20A IG Duplex, (2) 1/2" Diameter Holes for Low Voltage Wiring, Gray

Features

- Complete 3" Fire-Rated Poke-Through
- Prewired 20A IG Duplex Receptacle
- (2) 1/2" Diameter Holes for Low Voltage Wiring
- Non-metallic Cover with Painted Aluminum Flange
- Includes Junction Box

Specifications

Industry Standard(s)	• cULus Listed • Meets ADA Standards • UL 514A Listed
EU RoHS Indicator	No

Configuration

Number Of Outlets	(1) 20A Duplex IG Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
-------------------	---



General

Material - Mounting Hardware Specifications	Step-Down Installation • Cover Material - Thermoplastic cover with aluminum flange • Floor thickness - 2 1/4 to 7 in. (57.2 to 177.8) • Mounting - 3 in. (76.2) cored concrete diameter through hole
UPC	783585494197
Style	FRPT - Complete Kits
Application - For Use On	Carpet

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)