

SNAPConnect® Heavy Duty Hospital Grade
Tamper-Resistant/Weather Resistant
AUTOGUARD® Self-Test GFCI Receptacle,
15A, White

By Hubbell Wiring Device-Kellems
Catalog # [SNAPGFTW82W](#)

Straight Blade SNAPConnect® WRTR GFCI Hospital Grade
Receptacle, 15A

Features

- Audible SNAP, indicates solid connection
- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (406.12) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® Self-Test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Application

Commercial Hospital Grade

Specifications

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Environmental Conditions	Weather Resistant
Nema Rating	5-15R

Conductor

Wire Size	SNAPConnect®
-----------	--------------

Current

Phase	Single Phase
Current / Amperage Rating	15 A
Wattage	1875 W
Voltage Rating	125 VAC

Dimensions

Size	4.12 in x 1.75 in x 1.48 in
------	-----------------------------



Width	1.75 in
Height	4.12 in
Length	1.48 in
Dimensions	1.48 in x 1.75 in x 4.12 in

General

Item Type	Self test GFCI receptacle Tamper-Resistant, Weather Resistant
Series	Hospital Grade
Material	Nylon
Specifications	• Base - Nylon • Face - Nylon • Contacts - Brass • Mounting Screws - Stainless Steel • Mounting Strap - Brass • Power Contacts - Brass
UPC	783585746265
Color	White

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)