



USB Charger Hospital Grade Receptacle, 20A 125V Duplex, Power Delivery 55W Type C Ports, NEMA 5-20R, White

By Bryant
Catalog # [USB8300CPDW](#)

TR Receptacle, 2-Pole 3-Wire, NEMA 5-20R, USB 55W, 1 Type "C" PD, 1 Type "C" Standard 5V, White

Features

- High Power 55 Watt USB Power Delivery 3.0 Standard, 5 Volt USB BC1.2 Output
- Two Type C USB Ports, One Supports Power Delivery
- Tamper Resistant Hospital Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

Specifications

Industry Standard(s)	NEMA 5-20R, USB PD 3.0, USB BC1.2
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Current / Amperage Rating	20 A
---------------------------	------



Voltage Rating	125 V
General	
Type	Tamper Resistant USB
Series	Hospital Grade USB Charger
UPC	783585723402
Style	Style Line Decorator
Color	White

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)