

Bulk Cable, 10/3 STO, 280', White

By Hubbell Wiring Device-Kellems
Catalog # [WC310280](#)

Bulk Cable, 10/3 STO, 280', White



Features

- New improved styling
- Jute fillers inside jacket for maximum cable flexibility

Application

Ship-To-Shore Cables

Specifications

Industry Standard(s)	UL Listed
EU RoHS Indicator	Yes

Conductor

Conductor Type	Copper
Strands	Multi
Braid	None
Number Of Conductors	3

Configuration

Debris Shield Type	None
--------------------	------

Current

Amperage Rating	30 A
Voltage Rating	600V AC Max kV

Dimensions

Outside Diameter	0.335
Weight	0.36 lb.

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Material - Jacket	STW- PVC
Material - Insulation	Man Made Rubber
Specifications	• Cable Rating - 30A 10 Gauge/3 Wire STO- 280 ft. (85.3m) Roll • Product Type - Bulk Cable
UPC	783585765563
Color	White

Logistics

Carton Quantity	280
-----------------	-----

Operational

Temperature Rating	Limited by Devices
--------------------	--------------------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)