



# Filter Box Fan 115 Volt 630 Cubic Feet Per Minute 11.1X11.1

By Wiegmann  
Catalog # [FBF1010115V](#)

Filter Box Fan 115 Volt 630 Cubic Feet Per Minute 11.1X11.1



## Features

- Fan and grille are constructed of high grade steel
- Available in 115V or 230V
- High airflow and low noise operation
- Grille and filter can be removed and washed as needed

## Application

Cooling

## Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

## Current

Wattage	68 W
---------	------

## Dimensions

Actual Height	11.6 in
Actual Depth	4.8 in
Actual Width	11.8 in
Depth	5 in
Width	12 in
Height	12 in

## General

Type	Filter Box Fan
Material	Steel
UPC	786725885763
Color	Silver

## Logistics

Carton Quantity	4
Pallet Quantity	63

## Product Assets

[Catalog \[English\]](#)