



Filter Box Fan 115 Volt 239 Cubic Feet Per Minute 7.2X7.2

By Wiegmann
Catalog # [FBF66115V](#)

Filter Box Fan 115 Volt 239 Cubic Feet Per Minute 7.2X7.2



Features

- Fan and grille are constructed of high grade steel
- Available in 115V or 230V
- High airflow and low noise operation
- Grille and filter can be removed and washed as needed

Application

Cooling

Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Wattage	27 W
---------	------

Dimensions

Actual Height	7.6 in
Actual Depth	3.2 in
Actual Width	7.9 in
Depth	3 in
Width	8 in
Height	8 in

General

Type	Filter Box Fan
Material	Steel
UPC	786725885749
Color	Silver

Logistics

Carton Quantity	6
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)