



## NEMA 12 Filter Fan 115 Volt 340 Cubic Feet Per Minute 12.8X12.8 Light Gray

By Wiegmann

Catalog # [FF1313340CFM115VG](#)

NEMA 12 Filter Fan 115 Volt 340 Cubic Feet Per Minute 12.8X12.8 Light Gray



### Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

### Application

Ventilation; Temperature Control

### Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

### Dimensions

Actual Height	12.8 in
Actual Depth	6.3 in

Actual Width	12.8 in
Depth	6 in
Width	13 in
Height	13 in

### General

Type	Filter Fan
Material	ABS Plastic
UPC	786725886852
Color	Gray

### Logistics

Carton Quantity	4
Pallet Quantity	36

### Product Assets

[Catalog \[English\]](#)