



NEMA 12 Filter Fan 115 Volt 15 Cubic Feet Per Minute 4.2X4.2 -Light Gray

By Wiegmann

Catalog # [FF4415CFM115VG](#)

NEMA 12 Filter Fan 115 Volt 15 Cubic Feet Per Minute 4.2X4.2 - Light Gray



Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

Ventilation;Temperature Control

Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Voltage Rating	115 V
----------------	-------

Dimensions

Depth	3 in
-------	------

Mounting Depth	2.87 in
Actual Height	4.2 in
Actual Depth	3.1 in
Actual Width	4.2 in
Width	4 in
Height	4 in

General

Color	Gray
Cutout	3.63x3.63
Type	Filter Fan
Material	ABS Plastic
UPC	786725886395

Logistics

Carton Quantity	16
Pallet Quantity	512

Product Assets

[Catalog \[English\]](#)