



NEMA 12 Filter Fan 115 Volt 50 Cubic Feet Per Minute 5.9X5.9 -Light Gray

By Wiegmann

Catalog # [FF6650CFM115VG](#)

NEMA 12 Filter Fan 115 Volt 50 Cubic Feet Per Minute 5.9X5.9 - Light Gray



Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation.

Application

Ventilation;Temperature Control

Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Voltage Rating	115 V
----------------	-------

Dimensions

Depth	3 in
-------	------

Mounting Depth	2.56 in
Actual Height	5.9 in
Actual Depth	2.9 in
Actual Width	5.9 in
Width	6 in
Height	6 in

General

Color	Gray
Cutout	4.95x4.95
Type	Filter Fan
Material	ABS Plastic
UPC	786725886531

Logistics

Carton Quantity	20
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)