



## Fan Heater 115 Volt 20 Cubic Feet Per Minute 250 Watts

By Wiegmann  
Catalog # [FH115V250W](#)

Fan Heater 115 Volt 20 Cubic Feet Per Minute 250 Watts



### Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

### Application

Heating

### Specifications

Certified Listed	UL/cUL Recognized
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

### Current

Wattage	250 W
Voltage Rating	115 V

### Dimensions

Actual Height	5.3 in
Actual Depth	3.2 in
Actual Width	4.4 in
Depth	3 in
Width	4 in
Height	5 in

### General

Type	Fan Heater
Material	Plastic
UPC	786725886050
Color	Gray

### Logistics

Carton Quantity	1
Pallet Quantity	1

### Product Assets

[Catalog \[English\]](#)