



NEMA 4X Continuous Hinge Two Screw Cover 20X16X8 Fiberglass-White

By Wiegmann
Catalog # [HW-WHJ201608CHSC](#)

NEMA 4X Continuous Hinge Two Screw Cover 20X16X8
Fiberglass-White



*Representative Image

Features

- Constructed of molded fiberglass
- White enclosure with continuous hinge and two-screw cover
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	White
Cover Type	Hinged Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725879168

Dimensions

Cubic Capacity	2560 cu.in
Depth	8 in
Height	20 in
Weight	19.8 lb
Width	16 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-WHJ201608CHSC](#)
- [Catalogs - Wiegmann Non-Metallic Enclosures](#)
- [Engineering Drawing - HWDHW-WHJ201608CHSC-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand