

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.23"-0.32"

By Hubbell Premise Wiring
Catalog # [022291017](#)

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave,
Rod Closing, Tin-Coated Bronze, 0.23"-0.32"



Features

- For support when cable end is not available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes
Conductor	
Cable Diameter Range	0.23 in-0.32 in
Cable Size	.23"- .32" (.58-.81)

Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------

General

Construction

Material - Mounting Hardware
Type
Series
OEM Brand Name
Material
Specifications

Woven

Screw Hook or Beam Clamp
Single Eye
Fiber Optic
Hubbell Wiring Device-Kellems
Bronze, Tin Coated

- Eye - Stainless Steel
- Rod - Stainless Steel
- Strand - Tin-coated bronze
- Tag - Mylar

UPC
783585497945
Style
Split Mesh, Rod Closing, Single Weave

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)