

HUBBELL

Premise Wiring

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.18"-0.25"

By Hubbell Premise Wiring
Catalog # [022291000](#)

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.18"-0.25"

Features

- For permanent support when cable end is available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Conductor

Cable Diameter Range	0.18 in-0.25 in
Cable Size	.18"- .25" (.46-.63)

Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------



General

Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	• Eye - Stainless Steel • Strand - Tin-coated bronze • Tag - Mylar
UPC	783585332512
Style	Closed Mesh, Single Weave

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)