

# HUBBELL Premise Wiring

## Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.23"-0.32"

By Hubbell Premise Wiring  
Catalog # [022291001](#)

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.23"-0.32"



### Features

- For permanent support when cable end is available

### Application

Single Eye

### Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes

### Conductor

Cable Diameter Range	0.23 in-0.32 in
Cable Size	.23"- .32" (.58-.81)

### Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------

### General

### Construction

Material - Mounting Hardware  
Type  
Series  
OEM Brand Name  
Material  
Specifications

### Woven

Screw Hook or Beam Clamp  
Single Eye  
Fiber Optic  
Hubbell Wiring Device-Kellems  
Bronze, Tin Coated

- Eye - Stainless Steel
- Strand - Tin-coated bronze
- Tag - Mylar

783585332529  
Closed Mesh, Single Weave

UPC  
Style

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)