

HUBBELL
Premise Wiring

Fiber Optic Support Grips, Single Eye,
Closed Mesh, Single Weave, Tin-Coated
Bronze, 0.30"-0.39"

By Hubbell Premise Wiring
Catalog # [022291002](#)

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single
Weave, Tin-Coated Bronze, 0.30"-0.39"

Features

- For permanent support when cable end is available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes

Conductor

Cable Diameter Range	0.3 in-0.39 in
Cable Size	.30"-0.39" (.76-.99)

Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------



General

Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	• Eye - Stainless Steel • Strand - Tin-coated bronze • Tag - Mylar
UPC	783585332536
Style	Closed Mesh, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)