

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.37"-0.48"

By Hubbell Premise Wiring
Catalog # [022291003](#)

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.37"-0.48"

Features

- For permanent support when cable end is available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes

Conductor

Cable Diameter Range	0.37 in-0.48 in
Cable Size	.37"-.48" (.94-1.22)

Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------



General

Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	<ul style="list-style-type: none">• Eye - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar
UPC	783585332543
Style	Closed Mesh, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)