

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.46"-0.58"

By Hubbell Premise Wiring
Catalog # [022291004](#)

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.46"-0.58"

Features

- For permanent support when cable end is available

Application

Single Eye

Specifications

| | |
|----------------------|---------------|
| Industry Standard(s) | CSA Certified |
| EU RoHS Indicator | Yes |

Conductor

| | |
|----------------------|-----------------------|
| Cable Diameter Range | 0.46 in-0.58 in |
| Cable Size | .46"-.58" (1.17-1.47) |

Force Related

| | |
|--------------------------|---------|
| Approx Breaking Strength | 400 lb. |
|--------------------------|---------|



General

| | |
|------------------------------|--|
| Construction | Woven |
| Material - Mounting Hardware | Screw Hook or Beam Clamp |
| Type | Single Eye |
| Series | Fiber Optic |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Material | Bronze, Tin Coated |
| Specifications | <ul style="list-style-type: none">• Eye - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar |
| UPC | 783585332550 |
| Style | Closed Mesh, Single Weave |

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)