

HUBBELL
Premise Wiring

Fiber Optic Support Grips, Single Eye,
Closed Mesh, Single Weave, Tin-Coated
Bronze, 0.56"-0.71"

By Hubbell Premise Wiring
Catalog # 022291005

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single
Weave, Tin-Coated Bronze, 0.56"-0.71"

Features

- For permanent support when cable end is available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes

Conductor

Cable Diameter Range	0.56 in-0.71 in
Cable Size	.56"--.71" (1.42-1.80)

Force Related

Approx Breaking Strength	600 lb.
--------------------------	---------

General



Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	• Eye - Stainless Steel • Strand - Tin-coated bronze • Tag - Mylar
UPC	783585332567
Style	Closed Mesh, Single Weave

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)