

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.69"-0.88"

By Hubbell Premise Wiring
Catalog # [022291006](#)

Fiber Optic Support Grips, Single Eye, Closed Mesh, Single Weave, Tin-Coated Bronze, 0.69"-0.88"

Features

- For permanent support when cable end is available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes

Conductor

Cable Diameter Range	0.69 in-0.88 in
Cable Size	.69"-.88" (1.75-2.24)

Force Related

Approx Breaking Strength	800 lb.
--------------------------	---------



General

Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	<ul style="list-style-type: none">• Eye - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar
UPC	783585332574
Style	Closed Mesh, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)