

# HUBBELL Premise Wiring

## Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.18"-0.25"

By Hubbell Premise Wiring  
Catalog # [022291016](#)

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave,  
Rod Closing, Tin-Coated Bronze, 0.18"-0.25"



### Features

- For support when cable end is not available

### Application

Single Eye

### Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes
<b>Conductor</b>	
Cable Diameter Range	0.18 in-0.25 in
Cable Size	.18"- .25" (.46-.63)

### Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------

### General

### Construction

Material - Mounting Hardware  
Type  
Series  
OEM Brand Name  
Material  
Specifications

### Woven

Screw Hook or Beam Clamp  
Single Eye  
Fiber Optic  
Hubbell Wiring Device-Kellems  
Bronze, Tin Coated

- Eye - Stainless Steel
- Rod - Stainless Steel
- Strand - Tin-coated bronze
- Tag - Mylar

UPC  
Style

783585332659  
Split Mesh, Rod Closing, Single Weave

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)