

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.30"-0.39"

By Hubbell Premise Wiring
Catalog # [022291018](#)

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave,
Rod Closing, Tin-Coated Bronze, 0.30"-0.39"



Features

- For support when cable end is not available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes

Conductor

Cable Diameter Range	0.3 in-0.39 in
Cable Size	.30"-0.39" (.76-.99)

Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------

General

Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	<ul style="list-style-type: none">• Eye - Stainless Steel• Rod - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar
UPC	783585332673
Style	Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)