

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.37"-0.48"

By Hubbell Premise Wiring
Catalog # [022291019](#)

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave,
Rod Closing, Tin-Coated Bronze, 0.37"-0.48"



Features

- For support when cable end is not available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes
Conductor	
Cable Diameter Range	0.37 in-0.48 in
Cable Size	.37"-.48" (.94-1.22)

Force Related

Approx Breaking Strength	300 lb.
--------------------------	---------

General

Construction	Woven
--------------	-------

Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Fiber Optic
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Bronze, Tin Coated
Specifications	<ul style="list-style-type: none">• Equalizer - Bronze• Eye - Stainless Steel• Rod - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar
UPC	783585332680
Style	Split Mesh, Rod Closing, Single Weave

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)