

HUBBELL Premise Wiring

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave, Rod Closing, Tin-Coated Bronze, 0.46"-0.58"

By Hubbell Premise Wiring
Catalog # [022291020](#)

Fiber Optic Support Grips, Single Eye, Split Mesh, Single Weave,
Rod Closing, Tin-Coated Bronze, 0.46"-0.58"



Features

- For support when cable end is not available

Application

Single Eye

Specifications

Industry Standard(s)	CSA Certified
EU RoHS Indicator	Yes
Conductor	
Cable Diameter Range	0.46 in-0.58 in
Cable Size	.56"-.58" (1.17-1.47)

Force Related

Approx Breaking Strength	400 lb.
--------------------------	---------

General

Construction

Material - Mounting Hardware
Type
Series
OEM Brand Name
Material
Specifications

Woven

Screw Hook or Beam Clamp
Single Eye
Fiber Optic
Hubbell Wiring Device-Kellems
Bronze, Tin Coated

- Equalizer - Bronze
- Eye - Stainless Steel
- Rod - Stainless Steel
- Strand - Tin-coated bronze
- Tag - Mylar

UPC
Style

783585332697
Split Mesh, Rod Closing, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)