

Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Blue

By Hubbell Wiring Device-Kellems
Catalog # [5262BL](#)

Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V,
5-15R, Blue



Features

- Slender/compact design
- Finder Groove Face
- Triple wipe contacts

Application

Hubbell-Pro Extra Heavy Duty

Specifications

Environmental Conditions	Indoor Dry unless protected by additional means
EU RoHS Indicator	No
Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Wattage	1875 W

Voltage Rating 125 V

Dimensions

Display Size Standard Sized Product
Size Standard Sized Product

General

Series	Hubbell-PRO
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	Finder Groove Face
Color	Blue
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Type	Standard Duplex
Material	Thermoplastic/Composite
UPC	783585147178
Mounting Type	Screw Mount

Logistics

Carton Quantity 10

Operational

Temperature Rating

- Maximum continuous 75°C
- minimum -40°C (w/o impact)

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)