

## Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown

By Hubbell Wiring Device-Kellems  
Catalog # [5662B](#)

Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown



### Features

- Back and side wired
- Fed- Spec UL listed
- Smooth nylon face, Brass triple-wipe contacts

### Application

Hubbell-Pro Heavy Duty

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### Specifications

EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA 22.2, No. 42</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	6-15R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

### Current

Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	250 V
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Wattage	3750 W

### Dimensions

Weight	0.2 lb.
--------	---------

### General

Series	Hubbell-PRO
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	Smooth Face
Color	Brown
Material - Mounting Hardware	Screw Mounting
Type	Standard Duplex
UPC	783585555768

### Logistics

Carton Quantity	10
-----------------	----

### Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	1.5

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)