

Kellems Wire Management, Deluxe Cord Grips, Straight Male 1.250- 1.375", 2" with Mesh

By Hubbell Wiring Device-Kellems
Catalog # [074011258](#)

Kellems Wire Management, Deluxe Cord Grips, Straight Male
1.250- 1.375", 2" with Mesh



Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation
- UL514B Tray cable rated for dry locations

Application

Straight Male- Form 6

Performance

Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting), Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C, Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C), Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting

Specifications

Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL Listed

Conductor

Number Of Conductors	Single
Conductor Range	1.25-1.375 in (3.17-3.49 mm)

Cable Diameter Range	1.250 in-1.375 in
Cable Size	1.250"-1.375" (3.17-3.49)

Dimensions

Display Size	2" NPT
Thread Size	2" NPT

General

Series	Deluxe Cord Grips
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	For Insulated Cables
Item Type	Deluxe Cord Grips
Material - Mounting Hardware Type	Locknut or Tapped Opening Straight Male Thread
Material	Aluminum Fittings, Stainless Steel Mesh
Specifications	<ul style="list-style-type: none">• Body - Aluminum• Bushing - Neoprene• Nut - Aluminum• Strand - Stainless Steel
UPC	783585330860

Logistics

Carton Quantity	2
-----------------	---

Operational

Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
--------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)