

## Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems  
Catalog # [8200IVLTRA](#)

Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory



### Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

### Application

Hubbell-Pro Heavy Duty Hospital Grade

### Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94V-2, Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

### Specifications

EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA, C22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

### Current

Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A

Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Back and Side Wired
Wattage	1875 W
Voltage Rating	125 VAC

### Dimensions

Length	3.28 in
Width	1.57 in
Weight	0.2 lb.
Height	1.15 in
Dimensions	3.28 in x 1.57 in x 1.15 in

### General

Series	Hubbell-Pro
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	Smooth Face
Color	Ivory
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Type	Receptacle
Material	Nylon
Specifications	<ul style="list-style-type: none"> <li>• Automatic Self-grounding Staple - Stainless steel</li> <li>• Base - PBT</li> <li>• Clamping Plate - Plated steel</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> <li>• Mounting Screws - Zinc plated steel</li> <li>• Mounting Strap - Galvanized steel</li> <li>• Power Contacts - Brass</li> </ul>

UPC 783585542133

### Logistics

Carton Quantity	10
-----------------	----

### Operational

Indicator(s) Type	Green LED
-------------------	-----------

Operating Temperature

Maximum continuous 75°C and  
minimum -40°C without Impact  
0.5

Horsepower - Maximum

## Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
WDK-8200IVLTRA-SPEC-EN | REV 1/2026