

## Adapters, NEMA 5-15P to 15A NON-NEMA Locking

By Hubbell Wiring Device-Kellems  
Catalog # [9054A](#)



Adapters, NEMA 5-15P to 15A NON-NEMA Locking

### Features

- NEMA 5-15P to 15A NON-NEMA Locking

### Application

Heavy Duty

### Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

### Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

### Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In
Wattage	1875

Voltage Rating 125 VAC

### Dimensions

Display Size Standard Sized Product

### General

OEM Brand Name Hubbell Wiring Device-Kellems  
Color Black  
Item Type Plug-In Adapter  
Material Thermoplastic  
Specifications

- Female end - 10A 250V, 15A 125V Twist-Lock® slots
- Male end - 3 wire 15A, 125V straight blade grounding
- Product Type - Plug-In Adapters

UPC 783585779508

### Logistics

Carton Quantity 10

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)