

Hubbell-PRO

32 A, 100-130 VAC, 2-POLE, 3-WIRE

Splash Proof Receptacle



- Features
- IP44 environmental ratings
 - Impact and corrosion resistant insulated non-metallic housing
 - Sequential contact engagement to prevent a momentary over-voltage
 - Color coded housings provide quick identification of mating devices

Ordering Information

Description	Color	UPC Number	Catalog Number
Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle	Yellow	783585678429	C332R4SA

Listings


VDE, CE

Specifications

Application	High Ampacity Connections
Connection	Screwless Spring
Wire Size	#10AWG to #8AWG
Material	PBT
Mounting	Screw Mount

Performance

Electrical	
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V AC RMS
Mechanical	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are marked on device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions
Environmental	
Flammability	HB
Ingress Protection	IP44
Moisture Resistance	IEC 60309-1
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.



Complementary Products

Complementary Products Adapter Plate, Back Box

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

