

# HUBBELL Premise Wiring

## Replacement Knock-out Plate, Corrosion Resistant

By Hubbell Premise Wiring  
Catalog # [CFBKOPATECR](#)

Replacement Knock-out Plate, Corrosion Resistant



### Features

- Replacement Knock-Out Plate
- Epoxy Coated Finish
- Mounting Screws Included

### Application

For Use with Concrete Floor Boxes

### Specifications

Industry Standard(s)	UL 514
EU RoHS Indicator	Contact Manufacturer
<b>Conductor</b>	
Cable Entry	Concentric KO's
<b>Configuration</b>	
Knockouts	1) 3/4" - 1 1/4"
Mounting Method	Mounts to Box
<b>Dimensions</b>	
Size	Standard Sized Product
Width	2.78 in
Height	0.12 in

Length	2.88 in
Dimensions	2.88 in x 2.78 in x 0.12 in

### General

Construction Material - Main	Steel
Sub Brand	Concrete Floor Boxes
Construction	Steel
Type	Concrete Floor Box Accessory
Series	Recessed - CFB Series
Cover Type	<ul style="list-style-type: none"><li>• Rectangle</li><li>• Round</li></ul>
Material	Pre Galvanized Steel
Cover Shape	<ul style="list-style-type: none"><li>• Rectangle</li><li>• Round</li></ul>
UPC	783585447957
Accessory Type	Knock-out Plates
Application - For Use On	Concrete
Color	Metallic
Mounting Type	(4) Screw Mount

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)