

Specification Grade Commercial
Series, Toggle Switches, General
Purpose AC, Three Way, 15A
120/277V AC, Side Wired Only
Toggle

By Hubbell Wiring Device-Kellems
Catalog # [CS315I](#)



Switches and Lighting Controls, Specification Grade Commercial Series, Toggle Switches, General Purpose AC, Three Way, 15A 120/277V AC, Side Wired Only, Ivory Toggle.

Features

- Thread cleaning captive mounting screw
- Abuse resistant nylon toggle
- Steel, zinc plated bridge is corrosion resistant

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Action	SPDT
Catalog Number	CS315I
Color	Ivory
EU RoHS Indicator	Yes
Item Type	Three Way Toggle Switch
Material	Nylon
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	General Purpose
Specifications	• Auto Grounding Mounting Bridge - Zinc Plated Steel • Base Material - Thermoplastic, Black • Contacts - Silver Alloy • Ground Screw - Brass (Green)

	• Terminal Screws - Brass • Toggle Material - Nylon • Top Material - Thermoplastic, Gray
Style	Three Way
UPC	783585902050

Dimensions

Dimensions	4.18 in x 1.49 in x 1.83 in
Height	1.83 in
Length	4.18 in
Weight	0.15 lb
Width	1.49 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired Only
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	4500

Product Assets

[Catalog Page - WDK AA-44 Catalog Page](#)
[Catalog Page - WDK D-14 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - CS315I AutoCAD Drawing](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Sales Drawings - WDK_CS315_DRAWING_PDF](#)

[Specifications - CS315I Specification Sheet](#)
[Specifications - CS315I Specification Sheet French](#)
[Specifications - Wiring CS315I Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Marine Electrical Products](#)
[Video - Marine Electrical Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-CS315I-SPEC-EN | REV 4/2025