

Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS6364L](#)



Twist-Lock® Economy, Female Connector Body 50A125/250V

Features

- 50A 125/250V
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator Yes

Conductor

Number Of Wires 4-Wire
Wire Size #18 AWG to #8 AWG
Number Of Conductors 4-Wire Grounding
Conductor Range #6 AWG
Number Of Poles 3-Pole

Current

Current Rating 50 A
Amperage Rating 50 A
Voltage Rating Description 125/250 VAC
Connectivity Screw Terminals
Voltage Rating 125/250 VAC

Dimensions

Display Size Standard
Length 5.50 in
Width 2.40 in
Height 2.40 in
Dimensions 5.50 in x 2.40 in x 2.40 in

General

Series Replacement Part
Style Heavy Duty
Color Black
Item Type 50A Nylon Connector
Insulation Insulated Body
Material - Mounting Hardware Cord Mounted
Type Locking Connector
UPC 783585320687

Logistics

Carton Quantity 30
Pallet Quantity 1620

Operational

Temperature Rating

- Maximum Continuous: 75° C
- Minimum Continuous: -40° C w/o impact, -25° with impact.

Product Assets

[Catalog \[English\]](#)