



Locking Devices, Twist-Lock®, Economy, Receptacle, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8369L](#)

Twist-Lock® Economy, Receptacle 50A Non-NEMA



Features

- 50A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Industry Standard(s)	WR Rating

Conductor

Number Of Wires	4-Wire
Wire Size	#10 AWG to #4 AWG
Number Of Conductors	4-Wire Grounding
Conductor Range	#6 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	3 Phase 250V AC
Connectivity	Screw Terminals
Voltage Rating	3 Phase 250 VAC

Dimensions

Display Size	Standard
Length	3.30 in
Width	2.10 in
Height	2.40 in
Dimensions	3.30 in x 2.10 in x 2.40 in

General

Style	Heavy Duty
Color	Black
Item Type	50A Single Armored Heavy Duty Receptacle
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted Receptacle
Type	Receptacle
Material	Composite
UPC	783585320755

Logistics

Carton Quantity	30
Pallet Quantity	2340

Operational

Temperature Rating	<ul style="list-style-type: none">• Maximum Continuous: 75° C• Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)