

## Switches and Lighting Controls, Daylight Control, Dimming Ballasts, 0-10 Volt

By Hubbell Wiring Device-Kellems  
Catalog # [DHADC](#)

Switches and Lighting Controls, Daylight Control, Dimming Ballasts, 0-10 Volt

### Features

- 0-10V DC, Single zone continuous automatic dimming control
- Light-sensitivity range of 0-500 foot-candles
- Selectable 3- or 8-second dimming rate

### Application

For use with 0-10V DC dimming ballasts.

### Specifications

EU RoHS Indicator                      No

### Current



Voltage Rating Description	0-10V DC
Voltage Rating	0-10 VDC

### General

Series	Indoor
UPC	783585158532
Style	Photocell
Color	White

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)