

0-10V Dimmer
Combination Switch
Low Voltage Switches



Features

- 4-button switch
- Bi-level lighting & partial ON operation
- Pilot Light
- Single Gang Design

Ordering Information

Description	UPC Number	Catalog Number
0-10V dimmer combo LV switch	783585565057	DSC010GY

Listings

cULus

Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.3" L x 1.13" W x 1.13" D

Performance

Electrical	
Current Sinking Capacity	50mA
Power Requirements	Per switch: 10mA @ 30VDC Max
Environmental	
Operating Location	Indoor Use Only
Operating Temperature	32°to 122°F (0° to 50°C) Relative humidity (non-condensing): 10% to 90%



Complementary Products

Wallplate	NPS26GY
Wallplate, Decorator Opening, Snap-on	NP26GY
Wallplate, Decorator Opening	SS26
Wallplate, Decorator Opening, Stainless Steel	

Online Resources

eCatalog

