

Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Manual Set, 30A, 120/240V AC, 2', Black

By Hubbell Wiring Device-Kellems
Catalog # [GFP3305](#)

Power Protection Products, GFCI High Amperage Portables,
Industrial/Commercial, Manual Set, 30A 120/240V AC, 6' Cord
Length, 4-6 mA Trip Level, Black



Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral

Application

Line Cord Only No Devices

Performance

Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure, Electrical - Operating Voltage Range - 85% to 110%, Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC, Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency, Environmental - Construction - Industrial grade design, Environmental - Housing Rating - UL Type 4X, Environmental - Leakage Current - At 93% Humidity leakage current is zero, Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F, Environmental - Type - Meets UL943 Class A GFCI

Specifications

EU RoHS Indicator	No
Industry Standard(s)	cCSAus

Conductor

Strands	Multi
Number Of Conductors	4
Conductor Size	#10 AWG
Conductor Type	Copper

Current

Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	120/240 VAC
Current / Amperage Rating	30 A
Connectivity	Plug-In
Voltage Rating	120/240 VAC

Dimensions

Outside Diameter	0.335
Weight	4.5 lb.

General

Series	Extra Heavy Duty
OEM Brand Name	Hubbell Wiring Device-Kellems
Style	Manual Set
Color	Black
Item Type	Industrial Grade
Construction	Fabricated
Type	Portable, Straight Blade
Material - Jacket	PVC
Material - Insulation	Elastomer
Specifications	<ul style="list-style-type: none"> • Cord Type - 2-50', 10/3 SJGOOW. 100', 8/3 SEOW • Label Color - Black background with yellow lettering • Response Time - .025 sec. Max • Switch Interface - Double Insulated • Trip Level - 4 to 6 mA • Unit Color - Gray with black cover

UPC	783585521169
-----	--------------

Logistics

Carton Quantity	5
-----------------	---

Operational

Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)