

GFR8300SGI

By Hubbell Wiring Device-Kellems
Catalog # [GFR8300SGI](#)

Power Protection Products, Receptacles, GFCI, Safety Grade
Commercial Hospital Grade, Self Test, LED Indicator, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R, Ivory



Features

- 10kA Short Circuit Current Rating
- Limits improper access to energized contacts
- Power indication
- Ground fault indicator
- No power at face if reverse wired

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• Fed.Spec• Meets All NEC® Requirements
EU RoHS Indicator	No
Nema Rating	5-20R
Conductor	
Wire Size	#14 AWG to #12 AWG
Current	
Phase	Single Phase
Connectivity	Back and Side Wired Screw Terminals
Amperage Rating	20 A
Wattage	2500

Voltage Rating 125 V

General

Material - Mounting Hardware Type	Screw Mounting Tamper-Resistant, Weather Resistant
Material Specifications	Thermoplastic <ul style="list-style-type: none">• Base - PBT• Face - PBT• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Brass• Power Contacts - Brass
UPC	783585441061
Style	Standard
Color	Ivory

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)