



## Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Light Almond, US Product

By Bryant  
Catalog # [GFRST20LAU](#)

Straight Blade Devices, Receptacle, GFCI, Commercial Grade, Self Test, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Light Almond, US Product

### Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction

### Specifications

Industry Standard(s)	Meets All NEC® Requirements
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-20R

### Current

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

### General

Type	Standard
Series	Heavy Duty



### Specifications

- Base - Nylon
  - Face - Nylon
  - Ground Contacts - Brass
  - Mounting Screws - Zinc plated steel
  - Mounting Strap - Zinc plated steel
  - Power Contacts - Brass
- UPC  
Style  
Color
- 883778124242  
Assembled In USA  
Light Almond

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)