

GFRST82SNAPAL

By Hubbell Wiring Device-Kellems
Catalog # [GFRST82SNAPAL](#)

Straight Blade Devices, Receptacle, GFCI, SnapConnect,
Commercial Hospital Grade, Self Test, 15A 125V, 2-Pole 3- Wire
Grounding, 5-15R, Almond



General

Catalog Number	GFRST82SNAPAL
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Self test GFCI receptacle
Material	Nylon
Series	Hospital Grade
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Standard
UPC	783585486222

Dimensions

Dimensions	3.28 in x 1.77 in x 1.47 in
Height	1.47 in
Length	3.28 in
Width	1.77 in

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Wire Size	#12 AWG
-----------	---------

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - GFRST82SNAPAL AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2484_INSTALLINST](#)
[Literature - AUTOGUARD® Self Test Ground Fault Receptacles Literature - Duct Products Guide](#)
[Sales Drawings - WDK_GFRST82SNAP_DRAWING_PDF](#)
[Specifications - GFRST82SNAPAL Specification Sheet](#)
[Specifications - GFRST82SNAPAL](#)
[Specifications - Wiring GFRST82SNAPAL Specification Sheet](#)