

GFSMCB120151P

By Hubbell Wiring Device-Kellems
Catalog # [GFSMCB120151P](#)

Power Protection Product, GFCI Circuit Breakers, Industrial,
Single Pole, 15A 120V AC, GFCI Circuit Breaker Sensing Modules,
4-6 mA Trip Level, Black



Application

Heavy Duty Industrial Commercial

General

Actuator	Toggle
Auxiliary Contacts	None
Catalog Number	GFSMCB120151P
EU RoHS Indicator	No
Enclosure Type	None
Environmental Conditions	NEMA 4X with Supplied Gasket
Frame	Standard
Item Type	Circuit Breaker
Material	Composite
Number Of Poles	1-Pole
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
UPC	783585692203

Dimensions

Width	0.73 in
-------	---------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Interrupt Rating	10,000 A
Load Rating	80% of Full Rating Continuous A
Phase	Single Phase
Trip Range	4 to 6 mA in
Trip Type	.025 Seconds
Voltage Rating	120 VAC

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - M10061_ACAD](#)
[Installation Manuals - WIRING_PD2163_INSTALLINST](#)
[Sales Drawings - M10061](#)
[Sales Drawings - WDK_GFSMCB120_DRAWING_PDF](#)
[Specifications - GFSMCB120151P Specification Sheet English](#)
[Specifications - GFSMCB120151P Specification Sheet French](#)