

## GFSMCB240202P

By Hubbell Wiring Device-Kellems  
Catalog # [GFSMCB240202P](#)

Power Protection Product, GFCI Circuit Breakers, Industrial,  
Double Pole, 20A, 240V AC, GFCI Circuit Breaker Sensing  
Modules, 4-6 mA Trip Level, Black.



### Application

Heavy Duty Industrial Commercial

### General

Actuator	Toggle
Auxiliary Contacts	None
Catalog Number	GFSMCB240202P
EU RoHS Indicator	No
Enclosure Type	None
Environmental Conditions	NEMA 4X with Supplied Gasket
Frame	Standard
Item Type	Circuit Breaker
Material	Composite
Number Of Poles	2-Pole
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
UPC	783585692418

### Dimensions

Width	1.74 in
-------	---------

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Interrupt Rating	10,000 A
Load Rating	80% of Full Rating Continuous A
Phase	Single Phase
Trip Range	4 to 6 mA in
Trip Type	.025 Seconds
Voltage Rating	120 VAC

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - M10061\\_ACAD](#)  
[Installation Manuals - WIRING\\_PD2163\\_INSTALLINST](#)  
[Sales Drawings - M10061](#)  
[Sales Drawings - WDK\\_GFSMCB240\\_DRAWING\\_PDF](#)  
[Specifications - GFSMCB240202P Specification Sheet English](#)  
[Specifications - GFSMCB240202P Specification Sheet French](#)