

Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Back and Side Wired, Aluminum, NEMA 3R Enclosure with Switch

By Hubbell Wiring Device-Kellems
Catalog # [HBL13R89D](#)



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Back and Side Wired, Aluminum, NEMA 3R Enclosure with Switch

Features

- Optional Side Guard for close wall applications
- Clamping plate for secure back or side wiring
- Thermoset body provides resistance to electrical arc tracking

Application

Red Slide

Specifications

Industry Standard(s)	<ul style="list-style-type: none"> • CSA-C22.2 No.14 Industrial Control File LR-46186 • UL 508, Industrial Control File #E70402
EU RoHS Indicator	No

Current

Phase	Single Phase
Dielectric Strength	2,200V AC minimum for 1 minute
Connectivity	Pressure Terminal Screws
Current Rating	30 A
Amperage Rating	30 A
Wattage	18000 W

Dimensions

Width	4.4 in
Weight	1.55 lb.
Height	3.3 in
Length	5.52 in
Dimensions	5.52 in x 4.4 in x 3.3 in

Force Related

Load Capacity	Inductive
---------------	-----------

General

Material - Mounting Hardware	Screw Mounting
Type	Disconnect Switches
Specifications	Enclosure Material - Aluminum
UPC	783585202686
Style	Standard Duty

Logistics

Carton Quantity	4
-----------------	---

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Product Assets

[Catalog \[English\]](#)