

## Single Pole Devices and Temporary Power

150A, 600V AC/DC

### Female Plugs

# HUBBELL

#### Features

- Extra Long non-conductive inner sleeve
- Turn and Lock Symbol aids in the mating of devices
- Easily Identifiable Cable with cut off points for secure fit

#### Ordering Information

| Description   | Color | UPC Number   | Catalog Number |
|---|-------|--------------|----------------|
| 150A, thermoplastic elastomer, cable size #8 - #2 AWG | Brown | 783585511153 | HBL15FRSBN     |

#### Listings

UL and cUL Listed  
UL Enclosure Types 3R, 4X, 12  
National Electric Code (NEC), ANSI/NFPA 70

#### Specifications

|                          |                               |
|--------------------------|-------------------------------|
| Base Compound            | Thermoplastic Elastomer (TPE) |
| Contact Material         | Brass                         |
| Retaining Screw Material | Nylon                         |

#### Performance

##### Electrical

|                 |                    |
|-----------------|--------------------|
| Amperage Rating | 150A Maximum       |
| Voltage Rating  | 600V AC/DC Maximum |

##### Mechanical

|                        |  |
|------------------------|--|
| Product Identification | Ratings are a permanent part of device |
| Terminal Accommodation | #8 to #2 AWG                           |



#### Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

