

# Temporary Power Temporary Industrial Lighting LED Stringer Lights

# HUBBELL

## Features

- 90 LEDs for maximum illumination
- 10 fixtures spaced 10 feet apart for optimum light distribution
- Outdoor approved for wet locations

## Ordering Information

Description	UPC	Catalog Number
91 LEDs per fixture, light string	783585528304	HBL182S100LED



## Listings

UL  
CSA  
ETL

## Online Resources

[eCatalog](#)

## Specifications

Light Type	LED
Plug Type	NEMA 5-15P

## Performance

### Electrical

Lamp Life	50,000 hours
Lumen Output	450
Rating	15A 125V

### Mechanical

Cord Length	100 ft.
Number of fixtures	10
Watt per fixture	6.6

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

