

Surge Protective Devices, Plug-In, 1) Receptacle, 15A 125V, 750 Joules, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [HBL1PI750](#)

Surge Protective Devices, Plug-In, 1) Receptacle, 15A 125V, 750 Joules, Ivory



Features

- Plug-In
- 1) Receptacle
- 15A 125V
- 750 Joules

Application

Standard Devices and Cord Holder

Specifications

EU RoHS Indicator No

Current

Phase	Single Phase
Connectivity	Plug-In
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating	125 VAC

General

Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Material	Non-Metallic
Specifications	<ul style="list-style-type: none">• Joule Rating - 750• No.of Outlets - 1• Peak AMP Rating - 13.5kA
UPC	783585120935
Outlet	Straight Blade 5-15R

Operational

Indicator(s) Type	LED Indicator
Response Time	5
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish\]](#)