

Nylon Convenience Adapter, NEMA L5-20P To NEMA 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [HBL2129](#)

Nylon Convenience Adapter, NEMA L5-20P To NEMA 5-15R



Features

- Male Blade End
- Female Slot End

Application

Locking Male to Straight Blade Female

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL Listed
Nema Rating	L5-20P to 5-15R

Conductor

Number Of Wires	3-Wire Grounding
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Wattage	2500
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Plug-In Adapter
Material - Mounting Hardware	Plug-In
Material	Thermoplastic
Specifications	<ul style="list-style-type: none">• Female End - 5-20R, 20A 125V• Male End - L5-20P, 20A 125V• Product Type - Nylon Convenience Adapters
UPC	783585809014

Logistics

Carton Quantity	20
Pallet Quantity	2720

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)