

Adapter, Marine Use, NEMA 5-15P to NEMA L5-20R

By Hubbell Wiring Device-Kellems
Catalog # [HBL21CM28](#)

Marine Adapter 5 to NEMA



Features

- Marine Use
- NEMA 5-15P to NEMA L5-20R

Application

Straight Blade Male to Locking Female

Performance

Environmental - Moisture Resistance - IP20 Suitability

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL Listed
Nema Rating	5-15P to 5-20R

Conductor

Number Of Wires	3-Wire Grounding
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Wattage	2500
Voltage Rating	125 VAC

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Plug-In Adapter
Material - Mounting Hardware	Plug-In
Material	Thermoplastic
Specifications	<ul style="list-style-type: none">• Adapter Style - One Piece• Female End Rating - 20A 125V, 2P3W Twist-Lock®• Male End Rating - 15A 125V, 2P3W Straight Blade• Poles and Wires - 2 Pole, 3 Wire Grounding• Product Type - Adapters
UPC	783585808086

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)