

Adapter, Marine Use, NEMA L5-20P to NEMA 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [HBL21CM29](#)

Marine Adapter L5 to NEMA 5



Features

- Marine Use
- NEMA L5-20P to NEMA 5-15R

Application

Locking Male to Straight Blade Female

Performance

Environmental - Moisture Resistance - IP20 Suitability

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Standards - RoHS Compliance Status	CM
Nema Rating	L5-20P to 5-15R

Conductor

Number Of Wires	3-Wire Grounding
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In
Wattage	2500

Voltage Rating 125 VAC

Dimensions

Display Size Standard Sized Product

General

OEM Brand Name	Hubbell Wiring Device-Kellems
Color	White
Item Type	Plug-In Adapter
Material - Mounting Hardware	Plug-In
Material	Thermoplastic
Specifications	

- Adapter Style - One Piece
- Female End Rating - 15 or 20A 125V, 2P3W Straight Blade
- Male End Rating - 20A 125V, 2P3W Twist-Lock®
- Poles and Wires - 2 Pole, 3 Wire Grounding
- Product Type - Adapters

UPC 783585808093

Logistics

Carton Quantity 10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)